

TRADITIONAL WINDOW CLEANING SOAP, GLOVES



Quality Tools for Smart Cleaning



NINJA LIQUID



Window cleaning soap, liquid. Power formula with extended foam life.
 – High yield (concentrate 1:100)
 – Power formula with ultimate cleaning power for streak-free results
 – pH value 5,1 in aqueous solution

Part No.	Content	Pack
FR10S	1 l	12



NEW
from march 2024



Green Label LIQUID



Window cleaning soap, gel-like concentrate (1:100).
 – Can be applied directly to the washer sleeve or dissolved in water
 – pH value 5,1 in aqueous solution
 – Container made from recycled material
 – Made in Germany

Part No.	Content	Pack
GTL10	1 l	12



UNGER's LIQUID



Window cleaning soap, liquid. Concentrate. Mixing ratio 1:100.
 – Economic and eco-friendly
 – Excellent cleaning power
 – Simply add to water, pH value 6,9 in aqueous solution

Part No.	Content	Pack
FR100	1 l	12
FR500	5 l	2



UNGER's GEL



Window cleaning soap for direct application onto washer.
 – Economic, covers large areas
 – Excellent cleaning power
 – Apply directly onto washer, pH value 6,9 in aqueous solution

Part No.	Content	Pack
FG050	0.5 l	10



RUB OUT



Professional glass cleaner. Compact bottle with easy dispense cap.
 – Removes hard water stains, rust, mineral deposits, limescale and soap residue
 – Tough on stains, gentle on glass, pH value: 5
Attention: Some surfaces are easily scratched. Always test Rub Out prior to use.

Part No.	Content	Pack
RUB20	0.5 l	12



ErgoTec® NEOPRENE GLOVES



Gloves for window cleaning, made of 3 mm thick textile neoprene.
 – Tear resistant stitching and glue seal along seams for durability
 – Knuckle inserts and flexible curved shape for ultra comfort
 – Non slip palm with screened-on silicone for secure grip
 – Adjustable hooks & loops wrist strap

Part No.	Size	Hand circumference	Material	Pack
GL02S	7	18-19cm/ 7 in	Neoprene, textile	5
GL02L	8	20-21cm/ 8 in	Neoprene, textile	5
GL02X	9	22-23cm/ 9 in	Neoprene, textile	5
GL02Z	10	24-25cm/ 10 in	Neoprene, textile	5



NEOPRENE GLOVES



Gloves for window cleaning. Rubber Neoprene.
 – Tear resistant stitching and glue seal along seams for durability
 – Soft and comfortable on inside
 – Non slip palm for secure grip
 – Adjustable hooks & loops wrist strap


Part No.	Size	Hand circumference	Material	Pack
GLOV1	7	18-19cm/ 7 in	Neoprene, rubberized	10
GLOV2	8	20-21cm/ 8 in	Neoprene, rubberized	10
GLOV3	9	22-23cm/ 9 in	Neoprene, rubberized	10
GLOV4	10	24-25cm/ 10 in	Neoprene, rubberized	10



IDENTIFY YOUR GLOVE SIZE:

Measure the circumference of your hand at the widest point, right under the knuckles, excluding thumb.
 Check our size guide charts on the right to identify your glove size.

ATTENTION: Neoprene gloves run up to one size smaller. Our recommendation: Order one size larger than you usually wear.
 The tables provide guidelines for your glove size.
 We always recommend trying them on before buying!



* Palm: 50 % polyester, 50 % polyethylene; Back of the hand: 50 % nylon, 50 % polyethylene